
HEIDENHAIN



Machine Calibration

Fast, simple, accurate

www.heidenhain.com

Machine calibration with comparator systems from HEIDENHAIN, for optimal machining results

Fast


- Wide mounting tolerances
- Ready at all times
- Compact and easy to handle

Simple and robust

- Developed specifically for machine tools
- Wear-free
- Intuitive software

Highly accurate

- Superb system accuracy
- Stable accuracy, almost completely unaffected by surrounding conditions
- Contact-free measurement



Comparator system for rotary tables



RVM 4180

Specifications:

- System accuracy: ±0.5"
- Measuring range: 360°
- Measuring step: ≥ 0.03"
- Traversing speed: ≤ 100 rpm

Area of application:

Testing the static positioning accuracy in accordance with ISO 230-2, -3 and VDI/DGQ 3441



Space-optimized comparator measuring system for tilting axes

RVM 4280


Specifications:

- System accuracy: ±1.0"
- Measuring range: 360°
- Measuring step: ≥ 0.03"
- Traversing speed: ≤ 100 rpm

Characteristics:

- Space-optimized variant for calibrating tilting axes and other difficult-to-reach rotary axes
- Software-supported mounting design

Comparator measuring system for linear axes



KGM 281 und KGM 282

Specifications:

- Accuracy grade: ±1.0 μm
- Measuring range: ≤ 230 mm
- Measuring step: ≥ 0.001 µm
- Traversing speed: 72 m/min

Area of application:

- Circularity testing in accordance with ISO 230-4
- Free-form testing (2D contours)
- Acceptance testing in accordance with 10791-6 K2/K3
- Testing the static positioning accuracy in accordance with ISO 230-2, -3 and VDI/DGQ 3441



PC software for machine calibration





ACCOM 4.0

Characteristics:

- Add-on to hardware for a system solution
- Intuitive operation
- Separate measurement and evaluation functions
- Ability to export calibration charts and NC compensation tables

Area of application:

- Acceptance testing with the RVM 4x80
- Acceptance testing with the KGM 28x; replacement of ACCOM 3.2 (in progress)
- Continuously improved functionality



For more information



www.heidenhain.com/RVM4000



www.heidenhain.com/KGM200

HEIDENHAIN

DR. JOHANNES HEIDENHAIN GmbH

Dr.-Johannes-Heidenhain-Straße 5 **83301 Traunreut, Germany** [™] +49 8669 31-5000 [™] +49 8669 32-5061 E-mail: info@heidenhain.de

www.heidenhain.com



HEIDENHAIN worldwide